



FB6013007030



Trunking 60x130, grey

Technical properties

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

Compatibility

| | |
|---------------------------------------|--------------------------|
| Device installation compatible format | Standard 60mm, CEE, MCBs |
|---------------------------------------|--------------------------|

Connectivity

| | |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

Dimensions

| | |
|-----------------|---------|
| Trunking height | 61 mm |
| Length | 2000 mm |
| Trunking width | 130 mm |

Capacity

| | |
|--|----|
| Maximum number of cables (Ø 11 mm, 50% fill) | 27 |
| Maximum number of cables (Ø 11 mm, 50% fill) | 27 |

Cover, door

| | |
|--------------------------|----------|
| Lid mounting | External |
| Lid shape | loose |
| Lid width | 130 mm |
| Number of lids mountable | 1 |

Materials

| | |
|---------------------------|-----------|
| Material group | plastic |
| Type of surface treatment | untreated |
| Transparent | No |

Installation, mounting

| | |
|---------------|--------------------|
| Base punching | With base punching |
|---------------|--------------------|

Cable

| | |
|-------------------------------|----------------------|
| Internal/useful cross section | 6450 mm ² |
|-------------------------------|----------------------|

Equipment

| | |
|-------------------------------|-------|
| Number of plugable separators | 1 |
| Compartment quantity | 1 / 2 |
| Cable retainers per meter | 2 |

Standards

| | |
|-------------------------|----------------------|
| Approvals | EN50085-2-1 |
| European directive RoHS | voluntary compliance |

Safety

| | |
|-----------------|------|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |
| Impact strength | IK07 |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|

temperatur

| | |
|---------------------|------------|
| Ambient temperature | -5...65 °C |
|---------------------|------------|
