




G4703



## Input connector, 3 poles

### Technical properties

#### Architecture

Number of poles 3 P

#### Main electrical features

Nominal voltage 230 V

#### Voltage

Rated surge voltage 4 kV

#### Electric current

Rated current 25 A

#### Dimensions

Length 76 mm

Height 15 mm

Width 34.6 mm

#### Power

Fire load 0.117 kWh

#### Resistance

Continuity resistor 1 mΩ

#### Cover, door

Interlockable No

#### Materials

Colour black

Colour coding / contact insert black

Material Polyamid (PA)

Material group mixed material

#### Connection

Connection cross section (solid-core) 0.5 ; 4 mm<sup>2</sup>

Connection cross section (fine-strand) 0.5 ; 4 mm<sup>2</sup>

Type of connection with spring-loaded connection

#### Cable

Cable diameter 11 mm

#### Equipment

Contact Material Copper

Mechanical coding

Yes

**Standards**

European directive RoHS

voluntary compliance

**Safety**

Degree of contamination

3

REACH conform

Yes

RoHS conform

Yes

Locking mechanism

None