




G4713



Output connector, 3 poles

Technical properties

Architecture

Number of poles 3 P

Voltage

Rated surge voltage 4 kV

Electric current

Rated current 25 A

Dimensions

Length 76 mm

Height 15 mm

Width 34.6 mm

Power

Fire load 0.127 kWh

Resistance

Continuity resistor 1 mΩ

Cover, door

Interlockable No

Materials

Colour black

Colour coding / contact insert black

Material Polyamid (PA)

Material group mixed material

Type of surface treatment Tinned

Connection

Connection cross section (solid-core) 0.5 ; 4 mm²

Connection cross section (fine-strand) 0.5 ; 4 mm²

Cable

Cable diameter 11 mm

Equipment

Contact Material Copper

Mechanical coding Yes

Standards

Safety

Degree of contamination	3
Protection index IP	IP20
Locking mechanism	Integrated in plug-in connector
