




G4713



Output connector, 3 poles

Technical properties

Architecture

Number of poles 3 P

Main electrical features

Nominal voltage 230 V

Voltage

Rated surge voltage 4 kV

Electric current

Rated current 25 A

Dimensions

Length 76 mm

Height 15 mm

Width 34.6 mm

Power

Fire load 0.127 kWh

Resistance

Continuity resistor 1 mΩ

Cover, door

Interlockable No

Materials

Colour black

Colour coding / contact insert black

Material Polyamid (PA)

Material group mixed material

Connection

Connection cross section (solid-core) 0.5 ; 4 mm²

Connection cross section (fine-strand) 0.5 ; 4 mm²

Type of connection with spring-loaded connection

Cable

Cable diameter 11 mm

Equipment

Contact Material Copper

Mechanical coding

Yes

Standards

European directive RoHS

voluntary compliance

Safety

Degree of contamination

3

REACH conform

Yes

RoHS conform

Yes

Locking mechanism

Integrated in plug-in connector