



G4773



Technical properties

Architecture

Number of poles 3 P

Voltage

Max operating voltage 250 V

Rated surge voltage 4 kV

Electric current

Rated current 25 A

Dimensions

Length 51 mm

Height 32.7 mm

Width 30 mm

Power

Fire load 0.107 kWh

Resistance

Continuity resistor 1 mΩ

Cover, door

Interlockable Yes

Materials

Colour black

Colour coding / contact insert black

Material Polyamid (PA)

Material group mixed material

Type of surface treatment Tinned

Connection

Phase pickup none

Equipment

Number of outputs 2

Number of inputs 1

Contact Material Copper

Mechanical coding Yes

Standards

European directive RoHS voluntary compliance

Safety

Degree of contamination	3
Protection index IP	IP20
Max. continuous temperature resistance contact part	85 °C
Locking mechanism	Integrated in plug-in connector

temperatur

Max. continuous temperature resistance strain relief	105 °C
---	--------
