



G4773



Technical properties

Architecture

Number of poles	3 P
Type of pole	L PE N

Voltage

Max operating voltage	250 V
Rated surge voltage	4 kV

Electric current

Rated current	25 A
---------------	------

Dimensions

Length	51 mm
Height	32.7 mm
Width	30 mm

Power

Fire load	0.107 kWh
-----------	-----------

Resistance

Continuity resistor	1 mΩ
---------------------	------

Cover, door

Interlockable	Yes
---------------	-----

Materials

Colour coding / contact insert	black
Material group	mixed material

Connection

Phase pickup	none
--------------	------

Equipment

Number of outputs	2
Number of inputs	1
Contact Material	Copper
Mechanical coding	Yes

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Degree of contamination	3
REACH conform	Yes
RoHS conform	Yes
Max. continuous temperature resistance contact part	85 °C
Locking mechanism	Integrated in plug-in connector

temperatur

Max. continuous temperature resistance strain relief	105 °C
---	--------