



HA352

## Load break switch 3P 160A

### Technical properties

#### Architecture

Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

#### Functions

Reversing switch	No
------------------	----

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

#### Electric current

Rated operational current in AC21category B	160 A
Acceptable current rating with AC22 category A	160 A
Cut off current	3.6 kA
Rated current	160 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	7 kA
Thermal rated current outside of housings	160 A
Rated operational current in AC21 category A	160 A
Acceptable current rating with AC22 category B	160 A
Rated operational current in AC23 category A	160 A
Acceptable current rating with AC23 category B	160 A
Conventional thermal current under enclosure at 40°C	160 A

#### Dimensions

Depth of installed product	120 mm
Height of installed product	135 mm
Width of installed product	140 mm

**Power**

Nominal power under 440/500, 50Hz	55 kW
Total power loss under IN	9 W
Power loss per pole at In	3 W
Contact rating with 400 V in AC1	105 kW

**Cover, door**

Interlockable	Yes
---------------	-----

**Installation, mounting**

Fixation type	Back plate mounting
---------------	---------------------

**Connection**

Connection cross-sect. flexible conductor	95mm <sup>2</sup>
Type of connection	Terminal

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Width available for insulation connection	95 mm <sup>2</sup>
Motor drive optional	No

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP00
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-20...70 °C
-----------------------	-------------