



HA364

Load break switch 3P 1600A

Technical properties

Architecture

Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

Functions

Reversing switch	No
------------------	----

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

Voltage

Rated insulation voltage	1000 V
Rated impulse withstand voltage	12000 V

Electric current

Rated operational current in AC21 category B	1600 A
Acceptable current rating with AC22 category A	1250 A
Rated current	1600 A
Short-circuit current with gI-gG fuses	100 kA
Rated short-time withstand current 1s	50 kA
Thermal rated current outside of housings	1600 A
Rated operational current in AC21 category A	1600 A
Acceptable current rating with AC22 category B	1250 A
Rated operational current in AC23 category A	1000 A
Acceptable current rating with AC23 category B	1000 A
Conventional thermal current under enclosure at 40°C	1600 A

Power

Nominal power under 660 V, 50 Hz	475 kW
Active power under 380/415 V, 50 Hz	560 kW
Total power loss under I _N	366 W
Power loss per pole at I _n	122 W

Endurance

Number of mechanical operations	3000
---------------------------------	------

Cover, door

Interlockable	Yes
---------------	-----

Installation, mounting

Fixation type	Back plate mounting
---------------	---------------------

Connection

Type of connection	Terminal
--------------------	----------

Equipment

Number of auxiliary contacts as normally closed contact	0
---	---

Number of auxiliary contacts as normally open contact	0
---	---

Number of auxiliary contacts as change-over contact	0
---	---

Width available for insulation connection	185 mm ²
---	---------------------

Motor drive optional	No
----------------------	----

Standards

Standard text	IEC 60947-3
---------------	-------------

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP00
---------------------	------

Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------