



HA458

**Load break switch 4P 630A**

**Technical properties**

**Architecture**

Type of order	Long thumb-grip
Number of poles	4 P
Type of case	Fixed built-in

**Functions**

Reversing switch	No
------------------	----

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

**Voltage**

Rated insulation voltage	1000 V
Rated impulse withstand voltage	8000 V

**Electric current**

Rated operational current in AC21category B	630 A
Acceptable current rating with AC22 category A	630 A
Cut off current	45 kA
Rated current	630 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	13 kA
Rated operational current in AC21 category A	630 A
Acceptable current rating with AC22 category B	630 A
Rated operational current in AC23 category A	630 A
Acceptable current rating with AC23 category B	630 A

**Power**

Nominal power under 440/500, 50Hz	220 kW
Nominal power under 660 V, 50 Hz	150 kW
Active power under 380/415 V, 50 Hz	220 kW
Total power loss under IN	92.7 W
Power loss per pole at In	30.9 W

**Cover, door**

Interlockable	Yes
---------------	-----

**Installation, mounting**

Fixation type	Back plate mounting
---------------	---------------------

**Connection**

Connection cross-sect. rigid cable	2x300mm <sup>2</sup>
------------------------------------	----------------------

**Equipment**

Number of auxiliary contacts as normally closed contact	0
---	---

Number of auxiliary contacts as normally open contact	0
---	---

Number of auxiliary contacts as change-over contact	0
---	---

Width available for insulation connection	240 mm <sup>2</sup>
---	---------------------

Motor drive optional	No
----------------------	----

**Standards**

Standard text	IEC 60947-3
---------------	-------------

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP00
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

**Use conditions**

Operating temperature	-20...70 °C
-----------------------	-------------