



HAE310

Load break switch visible break. 3P 100A

Technical properties

Architecture

Type of order	Short thumb-grip
Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

Functions

Reversing switch	No
------------------	----

Configuration

Number of modules	6.22
-------------------	------

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

Electric current

Rated operational current in AC21category B	100 A
Rated current	100 A
Short-circuit current with gI-gG fuses	100 kA
Rated short-time withstand current 1s	4 kA
Acceptable current rating with AC22 category B	100 A
Rated operational current in AC23 category A	100 A
Acceptable current rating with AC23 category B	100 A

Power

Total power loss under I _N	9 W
Power loss per pole at I _N	3 W
Contact rating with 400 V in AC1	65 kW

Cover, door

Interlockable	Yes
---------------	-----

Installation, mounting

Tightening torque	4 - 4.4 Nm
-------------------	------------

Connection

Connection cross-sect. rigid cable	70mm ²
------------------------------------	-------------------

Type of connection	with screw
--------------------	------------

Equipment

Number of auxiliary contacts as normally closed contact	0
---	---

Number of auxiliary contacts as normally open contact	0
---	---

Number of auxiliary contacts as change-over contact	0
---	---

Width available for insulation connection	95 mm ²
---	--------------------

Motor drive optional	No
----------------------	----

Standards

Standard text	IEC 60947-3
---------------	-------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------