



HAD410

## Load break switch 4P 100A

### Technical properties

#### Architecture

Number of poles	4 P
Type of case	Fixed built-in

#### Functions

Reversing switch	No
------------------	----

#### Configuration

Number of modules	5.95
-------------------	------

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

#### Electric current

Rated current	100 A
Short-circuit current with gI-gG fuses	25 kA
Rated short-time withstand current 1s	2.75 kA
Rated operational current in AC23 category A	100 A

#### Power

Total power loss under I <sub>N</sub>	17.2 W
Power loss per pole at I <sub>N</sub>	4.3 W
Contact rating with 400 V in AC1	65 kW

#### Cover, door

Interlockable	Yes
---------------	-----

#### Connection

Type of connection	with screw
--------------------	------------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Number of auxiliary contacts as change-over contact	0
Width available for insulation connection	95 mm <sup>2</sup>
Motor drive optional	No
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-20...70 °C