



HBA125H

Electronic earth leakage add-on block 3P 125A I_{dn} adjustable, time delay

Technical properties

Architecture

Neutral position	not applicable
Number of poles	3 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage U _e	220 / 415 V
------------------------------------------	-------------

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
Rated current	125 A
Withstand not tripping on 8-20 μs wave	5 kA

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Tripping

Protected against nuisance tripping	Yes
-------------------------------------	-----

Connection

Connection cross-section at output with screw, for flexible conductor	2.5 / 70 mm ²
Connection cross-section at output with screw, for massive conductor	2.5 / 95 mm ²
Connection cross-section of input and output with screws, for massive conductors	2.5 / 95 mm ²
Connection cross section of access and exit with screws, for flexible conductor	2.5 / 70 mm ²

Settings

Rated fault current adjustable	Yes
Delay adjustable	Yes
Time delay of residual current	0 / 0.06 / 0.15 / 0.3 / 0.5 / 1 s

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Degree of pollution according to IEC 60664 /
IEC 60947-2

3

Altitude

2000 m