



HBA127H

## Electronic earth leakage add-on block 3P 125A Sensitivity fix

### Technical properties

#### Architecture

Number of poles	3 P
Fixing mode	DIN rail type O (symmetrical)

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
------------------------------	-------------

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

#### Electric current

Rated residual operating current	300 mA
Rated current	125 A
Withstand not tripping on 8-20 $\mu$ s wave	5 kA

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Tripping

Protected against nuisance tripping	Yes
-------------------------------------	-----

#### Connection

Connection cross-section at output with screw, for flexible conductor	2.5 / 70 mm <sup>2</sup>
Connection cross-section at output with screw, for massive conductor	2.5 / 95 mm <sup>2</sup>
Connection cross-section of input and output with screws, for massive conductors	2.5 / 95 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	2.5 / 70 mm <sup>2</sup>

#### Settings

Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Residual current type	A HI
REACH conform	No

RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m