



HCA126H

Switch X160 4P 125A

Technical properties

Architecture

Type of order	Toggle
Neutral position	left
Number of poles	4 P
Type of pole	4 P

Functions

Reversing switch	No
Trip Unit	SWITCH

Main electrical features

Rated operational voltage U_e	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV

Electric current

Rated current	125 A
Rated operational current in AC21	125 A

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

Power

Total power loss under I_N	33 W
Power loss per pole at I_N	11 W
Contact rating with 400 V in AC1	82 kW

Tripping

Time of response when opening	10 ms
-------------------------------	-------

Endurance

Electric endurance in number of cycles	10000
--	-------

Cover, door

Interlockable	Yes
---------------	-----

Materials

Toggle colour	Black
---------------	-------

Connection

Connection cross-sect. flexible conductor	4 / 70mm ²
Connection cross-sect. rigid cable	4 / 95mm ²
Connection	Front connection
Type of connection	with screw

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No

Use cases

Category of use	A
-----------------	---

Standards

Standard text	IEC 60947-3
---------------	-------------

Use conditions

Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Air humidity protection	95%HR 55°C sev Kn (IEC 68-2-30/52)
Storage/transport temperature	-35...70 °C