



HCJ401AR

Load Break Switch Disconnecter h3 x630 4P 400A FTC

Technical properties

Architecture

Type of order	Toggle
Neutral position	left
Number of poles	4 P
Type of pole	4 P
Fixing mode	fixing plate
Type of case	Fixed built-in

Functions

Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	Yes
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	SWITCH
Concurrently switching N-neutral	Yes

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

Electric current

Rated current	400 A
Rated short-time withstand current I _{cw}	5 kA
Rated short-time withstand current I _{cw} t=1s 220-240 V AC according IEC 60947-3	5 kA
Rated short-time withstand current I _{cw} t=1s 380-415 V AC according IEC 60947-3	5 kA
Rated operational current in AC21	400 A

Dimensions

Depth of installed product	150 mm
Height of installed product	260 mm
Width of installed product	185 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	116.1 W
---------------------------	---------

Power loss per pole at In	38.7 W
---------------------------	--------

Cover, door

Interlockable	Yes
---------------	-----

Materials

Toggle colour	Grey
---------------	------

Installation, mounting

Tightening torque	18Nm
-------------------	------

DIN rail mounting with optional adaptor	No
---	----

Suitable for front mounting center	No
------------------------------------	----

Suitable for front mounting	No
-----------------------------	----

Suitable for ground mounting	Yes
------------------------------	-----

Connection

Connection	Front connection
------------	------------------

Type of connection	Terminal
--------------------	----------

Cable

Cable Material	Cu
----------------	----

Equipment

Number of auxiliary contacts as normally closed contact	0
---	---

Number of auxiliary contacts as normally open contact	0
---	---

Number of auxiliary contacts as change-over contact	0
---	---

Motor drive optional	Yes
----------------------	-----

Can be accessorized	Yes
---------------------	-----

Use cases

Category of use	A
-----------------	---

Standards

Standard text	IEC 60947-3
---------------	-------------

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
temperatur	
Temp.-rise limits for access. parts (toggle) according to product standard	25 K
Temp.-rise limits for access. parts (not touched) according to product standard	50 K
Temp.rise limits for access. parts (to be touched) according to product standard	40 K
Temperature-rise limits for terminals according to the product standard	65 K