



HES040JC

**Moulded Case Circuit Breaker h3+ P160 LSI 3P3D 40A 70kA CTC**

**Technical properties**

**Architecture**

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of case	Fixed built-in

**Functions**

Complete device with protection unit	Yes
Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	LSI
Integrated earth fault protection	No

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage $U_e$	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	40 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 690V AC IEC 60947-2	6 kA
Rated short-time withstand current $I_{cw}$ $t=0.4s$ 220-240 V AC according IEC 60947-2	1.6 kA
Rated short-time withstand current $I_{cw}$ $t=0.4s$ 380-415 V AC according IEC 60947-2	1.6 kA
Rated short-time withstand current $I_{cw}$ $t=0.4s$ 660-690 V AC according IEC 60947-2	1.6 kA
Rating current 10°C according to IEC 60947	40 A
Rating current 15°C according to IEC 60947	40 A

Rating current 20°C according to IEC 60947	40 A
Rating current 25°C according to IEC 60947	40 A
Rating current 30°C according to IEC 60947	40 A
Rating current 35°C according to IEC 60947	40 A
Rating current 40°C according to IEC 60947	40 A
Rating current 45°C according to IEC 60947	40 A
Rating current 50°C according to IEC 60947	40 A
Rating current 55°C according to IEC 60947	40 A
Rating current 60°C according to IEC 60947	40 A
Rating current 65°C according to IEC 60947	40 A
Rating current 70°C according to IEC 60947	40 A
Rated service breaking capacity Ics under 660V AC according IEC 60947-2	6 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	2.5 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	2.5 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	2.5 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated service breaking capacity Ics under 110-138V AC according IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2	6 kA
<b>Dimensions</b>	
Depth of installed product	97 mm
Height of installed product	130 mm
Width of installed product	90 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Total power loss under IN	1.68 W
Power loss per pole at In	0.56 W
<b>Endurance</b>	
Electric endurance in number of cycles	10000
Number of mechanical operations	40000
<b>Cover, door</b>	

Interlockable	Yes
---------------	-----

---

**Installation, mounting**

Tightening torque	6Nm
DIN rail mounting with optional adaptor	Yes
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes

---

**Connection**

Connection cross-sect. rigid cable	6 / 95mm <sup>2</sup>
------------------------------------	-----------------------

---

**Protection**

Instantaneous protection (II): type	adjustable
-------------------------------------	------------

---

**Cable**

Cable Material	Cu
----------------	----

---

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
Can be accessorized	Yes

---

**Use cases**

Category of use	A
-----------------	---

---

**Use**

Vibrations and shocks withstand	IEC 68068-2-52 Test FC
---------------------------------	------------------------

---

**Standards**

Standard text	IEC 60947-2
European directive WEEE	concerned

---

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m

---

**temperatur**

Temperature of calibration	50 °C
----------------------------	-------