



HHA014Z

Moulded Case Circuit Breaker X160 1P 25kA 16A

Technical properties

Architecture

Number of poles	1 P
-----------------	-----

Functions

Complete device with protection unit	Yes
Trip Unit	TM F/F
Integrated earth fault protection	No

Configuration

Number of modules	1.5
-------------------	-----

Main electrical features

Rated operational voltage U_e	220 / 240 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	16 A
Rated ultimate short-circuit breaking capacity I_{cu} under 690V AC IEC 60947-2	4 kA
Thermal protection nob setting xIN	1
Breaking capacity on 1 pole for IT 230V NF 60947-2	21 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity I_{cs} AC according IEC 60947-2	80 %
Rated ultimate short-circuit breaking capacity I_{cu} under 230V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 240V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 415V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 440V AC IEC 60947-2	20 kA

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1
Power	
Total power loss under IN	1.8 W
Power loss per pole at In	1.8 W
Tripping	
Tripmode	TM
Thermal protection trip time	0 ms
Time of response when opening	10 ms
Electrical specifications	
Magnetic trip delay time	0 ms
Endurance	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Installation, mounting	
DIN rail mounting with optional adaptor	Yes
Connection	
Connection cross-sect. rigid cable	4 / 95mm ²
Settings	
Range of the magnetic adjustment	600 A
Setting type In or Ith	IN
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
Use cases	
Category of use	A
Standards	
Standard text	IEC 60947-2
European directive WEEE	concerned
Use conditions	
Operating temperature	-25...70 °C
Altitude	2000 m

Subject to technical modifications

