



HHA016Z

### Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 16A 25kA CTC

#### Technical properties

##### Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of case	Fixed built-in

##### Functions

Complete device with protection unit	Yes
Trip Unit	TM F/F
Integrated earth fault protection	No
Concurrently switching N-neutral	No

##### Controls and indicators

Motor drive integrated	No
------------------------	----

##### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

##### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

##### Electric current

Rated current	16 A
Thermal protection nob setting xIN	1
Rating current 10°C according to IEC 60947	21.5 A
Rating current 15°C according to IEC 60947	20.9 A
Rating current 20°C according to IEC 60947	20.2 A
Rating current 25°C according to IEC 60947	19.6 A
Rating current 30°C according to IEC 60947	18.9 A
Rating current 35°C according to IEC 60947	18.2 A
Rating current 40°C according to IEC 60947	17.5 A
Rating current 45°C according to IEC 60947	16.7 A
Rating current 50°C according to IEC 60947	16 A
Rating current 55°C according to IEC 60947	15.1 A
Rating current 60°C according to IEC 60947	14.2 A
Rating current 65°C according to IEC 60947	13.3 A

Rating current 70°C according to IEC 60947	12.3 A
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA
Range of the thermal adjustment	16 A
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	25 kA
<b>Dimensions</b>	
Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	75 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Total power loss under IN	5.3 W
Power loss per pole at In	1.8 W
<b>Endurance</b>	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
<b>Installation, mounting</b>	
DIN rail mounting with optional adaptor	No
<b>Settings</b>	
Range of the magnetic adjustment	600 A
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
Can be accessorized	Yes
<b>Standards</b>	
Standard text	IEC 60947-2
European directive WEEE	concerned
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m

