



HHA039Z

## Moulded Case Circuit Breaker X160 2P 25kA 40A

### Technical properties

#### Architecture

Number of poles	2 P
-----------------	-----

#### Functions

Complete device with protection unit	Yes
Trip Unit	TM F/F
Integrated earth fault protection	No

#### Configuration

Number of modules	4.5
-------------------	-----

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	40 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	4 kA
Thermal protection nob setting xIN	1
Breaking capacity on 1 pole for IT 230V NF 60947-2	21 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	80 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	20 kA

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1
<b>Power</b>	
Total power loss under I <sub>N</sub>	7.3 W
Power loss per pole at I <sub>N</sub>	3.7 W
<b>Tripping</b>	
Trip mode	TM
Thermal protection trip time	0 ms
Time of response when opening	10 ms
<b>Electrical specifications</b>	
Magnetic trip delay time	0 ms
<b>Endurance</b>	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
<b>Installation, mounting</b>	
DIN rail mounting with optional adaptor	Yes
<b>Connection</b>	
Connection cross-sect. rigid cable	4 / 95mm <sup>2</sup>
Type of connection	with screw
<b>Settings</b>	
Range of the magnetic adjustment	600 A
Setting type I <sub>N</sub> or I <sub>th</sub>	IN
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
<b>Standards</b>	
European directive WEEE	concerned
<b>Use conditions</b>	
Altitude	2000 m
Air humidity protection	for all climates