



HHB160Z

Moulded Case Circuit Breaker X250 3P 25kA 160A TM

Technical properties

Architecture

Type of order	Toggle
Number of poles	3 P
Type of pole	3P3D

Functions

Complete device with protection unit	Yes
Trip Unit	TM F/F
Integrated earth fault protection	No

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	160 A
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

Power

Total power loss under I _N	32.6 W
Power loss per pole at I _N	10.9 W

Tripping	
Tripmode	TM
Time of response when opening	10 ms
Endurance	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Installation, mounting	
DIN rail mounting with optional adaptor	Yes
Connection	
Connection cross-sect. flexible conductor	35 / 150mm ²
Connection cross-sect. rigid cable	35 / 185mm ²
Connection	Front connection
Type of connection	Terminal
Settings	
Range of the magnetic adjustment	2080 A
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Use cases	
Category of use	A
Standards	
Standard text	IEC 60947-2
European directive WEEE	concerned
Safety	
Protection index IP	IP4X
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C