



HHB201Z

## Moulded Case Circuit Breaker X250 4P 25kA 200A TM

### Technical properties

#### Architecture

Number of poles	4 P
-----------------	-----

#### Functions

Complete device with protection unit	Yes
Trip Unit	TM F/F
Integrated earth fault protection	No

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	200 A
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

#### Power

Total power loss under IN	38.4 W
Power loss per pole at In	12.8 W

#### Tripping

Tripmode	TM
----------	----

Time of response when opening	10 ms
-------------------------------	-------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Installation, mounting

DIN rail mounting with optional adaptor	Yes
---	-----

#### Connection

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Type of connection	Terminal

#### Settings

Range of the magnetic adjustment	2600 A
----------------------------------	--------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

#### Use cases

Category of use	A
-----------------	---

#### Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-25...70 °C
Altitude	2000 m
Storage/transport temperature	-35...70 °C