



HHB125Z

**Moulded Case Circuit Breaker X250 3P 25kA 125A TM**

**Technical properties**

**Architecture**

Type of order	Toggle
Number of poles	3 P

**Functions**

Complete device with protection unit	Yes
Trip Unit	TM F/F
Integrated earth fault protection	No

**Main electrical features**

Rated operational voltage Ue	220 / 415 V
------------------------------	-------------

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	125 A
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA

**Current correction factors**

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

**Power**

Total power loss under I <sub>N</sub>	27.7 W
Power loss per pole at I <sub>N</sub>	9.2 W

**Tripping**

Tripmode	TM
----------	----

Time of response when opening	10 ms
-------------------------------	-------

---

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

---

**Installation, mounting**

DIN rail mounting with optional adaptor	Yes
---	-----

---

**Connection**

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
Connection	Front connection

---

**Settings**

Range of the magnetic adjustment	1625 A
----------------------------------	--------

---

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

---

**Use cases**

Category of use	A
-----------------	---

---

**Standards**

Standard text	IEC 60947-2
European directive WEEE	concerned

---

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

---

**Use conditions**

Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C