



HI462



Change-over switch 4P 1250A

Technical properties

Architecture

Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

Functions

Reversing switch	Yes
------------------	-----

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	380 / 400 / 500 / 690 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	1000 V
Rated impulse withstand voltage	12000 V
Rated operational voltage in DC	260 / 400 / 500 V

Electric current

Rated operational current in AC21 category B	1250 A
Acceptable current rating with AC22 category A	1250 A
Rated current	1250 A
Short-circuit current with gI-gG fuses	100 kA
Rated short-time withstand current 1s	35 kA
Thermal rated current outside of housings	1250 A
Rated operational current in AC21 category A	1250 A
Acceptable current rating with AC22 category B	1250 A
Rated operational current in AC23 category A	630 A
Acceptable current rating with AC23 category B	1250 A

Dimensions

Depth of installed product	375 mm
Height of installed product	330 mm
Width of installed product	466 mm

Power

Nominal power under 440/500, 50Hz	710 kW
Nominal power under 660 V, 50 Hz	600 kW
Active power under 380/415 V, 50 Hz	710 kW
Total power loss under IN	279.9 W
Power loss per pole at In	93.3 W
Contact rating with 400 V in AC1	822 kW

Endurance

Electrical durability at nominal load in AC21 in operating cycles	500
Electrical durability at nominal load in AC22 in operating cycles	100
Number of mechanical operations	4000

Cover, door

Interlockable	Yes
---------------	-----

Connection

Type of connection	Terminal
--------------------	----------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No

Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

Safety

Protection index IP	IP00
---------------------	------

Use conditions

Operating temperature	-20...70 °C
Storage/transport temperature	-40...65 °C