



HIM304

## Modular change-over switch 3x40A

### Technical properties

#### Architecture

Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

#### Functions

Reversing switch	Yes
------------------	-----

#### Configuration

Number of modules	6
-------------------	---

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Electric current

Rated operational current in AC21 category B	40 A
Acceptable current rating with AC22 category A	40 A
Rated current	40 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	1.26 kA
Rated operational current in AC21 category A	40 A
Acceptable current rating with AC22 category B	40 A
Rated operational current in AC23 category A	40 A
Acceptable current rating with AC23 category B	40 A

#### Power

Total power loss under I <sub>N</sub>	2.7 W
Power loss per pole at I <sub>N</sub>	0.9 W
Contact rating with 400 V in AC1	26 kW

**Endurance**

---

Number of mechanical operations	10000
---------------------------------	-------

**Cover, door**

---

Interlockable	Yes
---------------	-----

**Equipment**

---

Number of auxiliary contacts as normally closed contact	0
---	---

---

Number of auxiliary contacts as normally open contact	0
---	---

---

Number of auxiliary contacts as change-over contact	0
---	---

---

Motor drive optional	No
----------------------	----

**Standards**

---

Standard text	IEC 60947-3
---------------	-------------

---

European directive WEEE	concerned
-------------------------	-----------

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	-20...70 °C
-----------------------	-------------