



HMS064BC

Moulded Case Circuit Breaker h3+ P160 MAG 4P4D 63A 50kA CTC

Technical properties

Architecture

Neutral position	left
Number of protected poles	4
Number of poles	4 P
Fixing mode	fixing plate
Type of case	Fixed built-in

Functions

Complete device with protection unit	Yes
Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	MAG (ICB)
Integrated earth fault protection	No
Concurrently switching N-neutral	Yes

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	63 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	6 kA
Rated service breaking capacity Ics under 660V AC according IEC 60947-2	6 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	6 kA

Breaking capacity on 1 pole for IT 415V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 690V NF 60947-2	2.5 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Rated service breaking capacity Ics under 110-138V AC according IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2	6 kA

Dimensions

Depth of installed product	97 mm
Height of installed product	130 mm
Width of installed product	120 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	10.5 W
Power loss per pole at In	3.5 W

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

Cover, door

Interlockable	Yes
---------------	-----

Installation, mounting

Tightening torque	6Nm
DIN rail mounting with optional adaptor	Yes
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes

Connection

Connection cross-sect. rigid cable	6 / 95mm²
Type of connection	with screw

Protection	
Instantaneous protection (li): type	fixed
Cable	
Cable Material	Cu
Settings	
Range of the magnetic adjustment	378 / 504 / 630 / 756 A
Magnetic protection nob setting xIN	6 / 8 / 10 / 12
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
Can be accessorized	Yes
Use	
Vibrations and shocks withstand	IEC 68068-2-52 Test FC
Standards	
European directive WEEE	concerned
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m