



HMS025DC

Moulded Case Circuit Breaker h3+ P160 TM ADJ 3P3D 25A 50kA CTC

Technical properties

Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Fixing mode	fixing plate
Type of case	Fixed built-in

Functions

Complete device with protection unit	Yes
Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	TM A/A
Integrated earth fault protection	No

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	25 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	6 kA
Thermal protection nob setting xI _N	0.63 / 0.8 / 1
Rating current 10°C according to IEC 60947	30.1 A
Rating current 15°C according to IEC 60947	29.6 A
Rating current 20°C according to IEC 60947	28.9 A
Rating current 25°C according to IEC 60947	28.3 A
Rating current 30°C according to IEC 60947	27.7 A

Rating current 35°C according to IEC 60947	27 A
Rating current 40°C according to IEC 60947	26.4 A
Rating current 45°C according to IEC 60947	25.7 A
Rating current 50°C according to IEC 60947	25 A
Rating current 55°C according to IEC 60947	24.3 A
Rating current 60°C according to IEC 60947	23.5 A
Rating current 65°C according to IEC 60947	22.8 A
Rating current 70°C according to IEC 60947	22 A
Rated service breaking capacity Ics under 660V AC according IEC 60947-2	6 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 690V NF 60947-2	2.5 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Range of the thermal adjustment	16 / 20 / 25 A
Rated service breaking capacity Ics under 110-138V AC according IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2	6 kA
Dimensions	
Depth of installed product	97 mm
Height of installed product	130 mm
Width of installed product	90 mm
Frequency	
Frequency	50 to 60 Hz
Power	
Power loss per pole at 0.63*In	2.66 W
Power loss per pole at 0.8*In	4.16 W
Total power loss at 0.63*In	7.99 W
Total power loss at 0.8*In	12.48 W
Total power loss under IN	19.5 W
Power loss per pole at In	6.5 W
Tripping	
Short-time delayed tripping	No

Subject to technical modifications

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

Cover, door

Interlockable	Yes
---------------	-----

Installation, mounting

Tightening torque	6Nm
DIN rail mounting with optional adaptor	Yes
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes

Connection

Connection cross-sect. rigid cable	6 / 95mm ²
Type of connection	with screw

Protection

Instantaneous protection (li): type	fixed
-------------------------------------	-------

Cable

Cable Material	Cu
----------------	----

Settings

Range of the magnetic adjustment	150 / 200 / 250 / 300 A
Magnetic protection nob setting xIN	6 / 8 / 10 / 12

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
Can be accessorized	Yes

Use

Vibrations and shocks withstand	IEC 68068-2-52 Test FC
---------------------------------	------------------------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Altitude	2000 m
temperatur	
Temperature of calibration	50 °C