



HMT250NR

**Moulded Case Circuit Breaker h3+ P250 Energy 3P3D 250A 50kA FTC**

**Technical properties**

**Architecture**

Type of order	Toggle
Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3P3D
Fixing mode	Screwed
Type of case	Fixed built-in

**Functions**

Complete device with protection unit	Yes
Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	ENERGY
Integrated earth fault protection	No

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage $U_e$	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	250 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 690V AC IEC 60947-2	6 kA
Rated short-time withstand current $I_{cw}$ $t=0.4s$ 220-240 V AC according IEC 60947-2	2.5 kA
Rated short-time withstand current $I_{cw}$ $t=0.4s$ 380-415 V AC according IEC 60947-2	2.5 kA

Rated short-time withstand current I <sub>cs</sub> t=0.4S 660-690 V AC according IEC 60947-2	2.5 kA
Rating current 10°C according to IEC 60947	250 A
Rating current 15°C according to IEC 60947	250 A
Rating current 20°C according to IEC 60947	250 A
Rating current 25°C according to IEC 60947	250 A
Rating current 30°C according to IEC 60947	250 A
Rating current 35°C according to IEC 60947	250 A
Rating current 40°C according to IEC 60947	250 A
Rating current 45°C according to IEC 60947	250 A
Rating current 50°C according to IEC 60947	250 A
Rating current 55°C according to IEC 60947	250 A
Rating current 60°C according to IEC 60947	250 A
Rating current 65°C according to IEC 60947	250 A
Rating current 70°C according to IEC 60947	238.3 A
Rated service breaking capacity I <sub>cs</sub> under 660V AC according IEC 60947-2	6 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	2.5 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	2.5 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	2.5 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 230V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 415V AC IEC 60947-2	50 kA
Rated service breaking capacity I <sub>cs</sub> under 110-138V AC according IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 220V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 380V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 660V AC IEC 60947-2	6 kA
<b>Dimensions</b>	
Depth of installed product	97 mm
Height of installed product	165 mm
Width of installed product	105 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Total power loss under I <sub>N</sub>	45 W
Power loss per pole at I <sub>N</sub>	15 W
<b>Endurance</b>	
Electric endurance in number of cycles	10000

Subject to technical modifications

Number of mechanical operations	40000
---------------------------------	-------

---

**Cover, door**

Interlockable	Yes
---------------	-----

---

**Installation, mounting**

Tightening torque	12Nm
-------------------	------

DIN rail mounting with optional adaptor	No
---	----

Suitable for front mounting center	No
------------------------------------	----

Suitable for front mounting	No
-----------------------------	----

Suitable for ground mounting	Yes
------------------------------	-----

---

**Connection**

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
---	-------------------------

Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
------------------------------------	-------------------------

Connection	Front connection
------------	------------------

Type of connection	Terminal
--------------------	----------

---

**Protection**

Instantaneous protection (II): type	adjustable
-------------------------------------	------------

---

**Cable**

Cable Material	Cu / Al
----------------	---------

---

**Equipment**

Number of auxiliary contacts as normally closed contact	0
---	---

Number of auxiliary contacts as normally open contact	0
---	---

Number of auxiliary contacts as change-over contact	0
---	---

Motor drive optional	Yes
----------------------	-----

Can be accessorized	Yes
---------------------	-----

---

**Use cases**

Category of use	A
-----------------	---

---

**Use**

Vibrations and shocks withstand	IEC 68068-2-52 Test FC
---------------------------------	------------------------

---

**Standards**

Standard text	IEC 60947-2
---------------	-------------

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

Protection index IP	IP4X
---------------------	------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

---

**Use conditions**

Degree of pollution according to IEC 60664 /  
IEC 60947-2

3

Altitude

2000 m

Air humidity protection

95%HR 55°C sev Kn (IEC 68-2-30/52)