



HMX263



## MCB 2P 50kA C-63A 3M

### Technical properties

#### Architecture

Number of protected poles	2
Number of poles	2 P
Type of pole	2 P
Curve	C

#### Functions

Concurrently switching N-neutral	No
----------------------------------	----

#### Configuration

Number of modules	3
-------------------	---

#### Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	50 kA
Rated operational voltage $U_e$	415 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

#### Electric current

Rated current	63 A
min/maxi threshold value of the AC thermal operation	1.05 / 1.3 $I_n$
Magnetic regulating current	5 / 10 $I_n$
Rating current -10°C according to IEC 60947	83.75 A
Rating current -15°C according to IEC 60947	85.55 A
Rating current -20°C according to IEC 60947	87.31 A
Rating current -25°C according to IEC 60947	89.04 A
Rating current -5°C according to IEC 60947	81.92 A

Rating current 0°C according to IEC 60947	80.03 A
Rating current 10°C according to IEC 60947	76.13 A
Rating current 15°C according to IEC 60947	74.11 A
Rating current 20°C according to IEC 60947	72.02 A
Rating current 25°C according to IEC 60947	69.88 A
Rating current 30°C according to IEC 60947	67.66 A
Rating current 35°C according to IEC 60947	65.37 A
Rating current 40°C according to IEC 60947	63 A
Rating current 45°C according to IEC 60947	60.53 A
Rating current 5°C according to IEC 60947	78.11 A
Rating current 50°C according to IEC 60947	57.96 A
Rating current 55°C according to IEC 60947	55.27 A
Rating current 60°C according to IEC 60947	52.45 A
Rating current 65°C according to IEC 60947	49.46 A
Rating current 70°C according to IEC 60947	46.28 A
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	50 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	4.5 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	4.5 kA
Rated service breaking capacity Ics AC according IEC 60947-2	50 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
<b>Current correction factors</b>	
Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85
<b>Dimensions</b>	
Depth of installed product	70 mm
Height of installed product	90 mm
Width of installed product	53 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Total power loss under IN	10.83 W
Power loss per pole at In	5.45 W

Subject to technical modifications

<b>Endurance</b>	
Electric endurance in number of cycles	4000
Number of mechanical operations	20000
<b>Installation, mounting</b>	
Type of top connection for modular devices	with screw
Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	plastic
Type of Bottom Connection for modular devices	with screw
Top removability for modular devices	Yes
Bottom removability for modular devices	Yes
<b>Connection</b>	
Connection cross-section at output with screw, for flexible conductor	1 / 50 mm <sup>2</sup>
Connection cross-section at output with screw, for massive conductor	1 / 70 mm <sup>2</sup>
Connection cross-section for rigid conductor, upstream terminals with screws	1 / 70 mm <sup>2</sup>
Connection cross-section of the access with screws, with flexible conductor	1 / 50 mm <sup>2</sup>
Connection cross-section of input and output with screws, for massive conductors	1 / 70 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1 / 50 mm <sup>2</sup>
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Class of energy limitation I <sup>2</sup> t	3
Altitude	2000 m
Air humidity protection	for all climates
<b>temperatur</b>	
Temperature of calibration	40 °C