



HMX350



MCB 3P 50kA C-50A 4.5M

Technical properties

Architecture

Number of protected poles	3
Number of poles	3 P
Type of pole	3 P
Curve	C

Functions

Concurrently switching N-neutral	No
----------------------------------	----

Configuration

Number of modules	4.5
-------------------	-----

Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

Main electrical features

Rated short circuit breaking capacity I _{cn} AC according IEC60898-1	50 kA
Rated operational voltage U _e	415 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

Electric current

Rated current	50 A
min/maxi threshold value of the AC thermal operation	1.05 / 1.3 I _n
Magnetic regulating current	5 / 10 I _n
Rating current -10°C according to IEC 60947	65.79 A
Rating current -15°C according to IEC 60947	67.17 A
Rating current -20°C according to IEC 60947	68.52 A
Rating current -25°C according to IEC 60947	69.84 A
Rating current -5°C according to IEC 60947	64.39 A

Rating current 0°C according to IEC 60947	62.95 A
Rating current 10°C according to IEC 60947	59.98 A
Rating current 15°C according to IEC 60947	58.43 A
Rating current 20°C according to IEC 60947	56.85 A
Rating current 25°C according to IEC 60947	55.21 A
Rating current 30°C according to IEC 60947	53.53 A
Rating current 35°C according to IEC 60947	51.8 A
Rating current 40°C according to IEC 60947	50 A
Rating current 45°C according to IEC 60947	48.14 A
Rating current 5°C according to IEC 60947	61.48 A
Rating current 50°C according to IEC 60947	46.2 A
Rating current 55°C according to IEC 60947	44.17 A
Rating current 60°C according to IEC 60947	42.05 A
Rating current 65°C according to IEC 60947	39.82 A
Rating current 70°C according to IEC 60947	37.45 A
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	50 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	4.5 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	4.5 kA
Rated service breaking capacity Ics AC according IEC 60947-2	50 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Current correction factors	
Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85
Dimensions	
Depth of installed product	70 mm
Height of installed product	90 mm
Width of installed product	80 mm
Frequency	
Frequency	50 to 60 Hz
Power	
Total power loss under IN	11.46 W
Power loss per pole at In	3.92 W

Subject to technical modifications

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	3,5 to 5Nm
Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	plastic
Type of Bottom Connection for modular devices	with screw
Top removability for modular devices	Yes
Bottom removability for modular devices	Yes

Connection

Connection cross-section at output with screw, for flexible conductor	1 / 50 mm ²
Connection cross-section at output with screw, for massive conductor	1 / 70 mm ²
Connection cross-sect. flexible conductor	50mm ²
Connection cross-sect. rigid cable	70mm ²
Connection cross-section for rigid conductor, upstream terminals with screws	1 / 70 mm ²
Connection cross-section of the access with screws, with flexible conductor	1 / 50 mm ²
Connection cross-section of input and output with screws, for massive conductors	1 / 70 mm ²
Connection cross section of access and exit with screws, for flexible conductor	1 / 50 mm ²
Type of connection	terminal with tightening compensation system

Standards

Standard text	IEC 60947-2
---------------	-------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Class of energy limitation I ² t	3
Altitude	2000 m
Air humidity protection	for all climates

temperatur

Temperature of calibration	40 °C
----------------------------	-------