



HNB160H

## Moulded Case Circuit Breaker X250 3P 40kA 160A TM

### Technical properties

#### Architecture

Neutral position	without neutral
Number of poles	3 P

#### Functions

Complete device with protection unit	Yes
Trip Unit	TM A/A
Integrated earth fault protection	No

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	160 A
Thermal protection nob setting xIN	0.63 / 0.8 / 1
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	40 kA

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

#### Power

Total power loss under IN	32.6 W
Power loss per pole at IN	10.9 W

<b>Tripping</b>	
Tripmode	TM
Time of response when opening	10 ms
<b>Endurance</b>	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
<b>Installation, mounting</b>	
DIN rail mounting with optional adaptor	Yes
<b>Connection</b>	
Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Type of connection	Terminal
<b>Settings</b>	
Range of the magnetic adjustment	960 / 1280 / 1600 / 2080 A
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C