



HNE971H

## Moulded Case Circuit Breaker h1000 4P 50kA 1000A LSI

### Technical properties

#### Architecture

Number of poles	4 P
Type of pole	4 P

#### Functions

Complete device with protection unit	Yes
Trip Unit	LSI
Integrated earth fault protection	No

#### Configuration

Number of modules	16
-------------------	----

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	1000 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0.4 / 0.5 / 0.63 / 0.8 / 0.9 / 0.95 / 1
Thermal setting current on neutral pole	0 / 0.5 / 1 In
Breaking capacity on 1 pole for IT 230V NF 60947-2	45 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	100 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	75 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	45 kA

**Current correction factors**

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

**Power**

Total power loss under IN	186 W
Power loss per pole at In	62 W

**Tripping**

Tripmode	LSI
Thermal protection trip time	5 / 10 / 11 / 16 / 21 ms
Time of response when opening	10 ms

**Electrical specifications**

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Installation, mounting**

DIN rail mounting with optional adaptor	No
-----------------------------------------	----

**Connection**

Type of connection	Terminal
--------------------	----------

**Settings**

Range of the magnetic adjustment	5600 / 7000 / 8820 / 10000 / 10000 / 10000 / 10000 A
Magnetic protection nob setting xIN	2.5 / 5 / 8
Setting type In or Ith	IrTh

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

**Use cases**

Category of use	A
-----------------	---

**Standards**

Standard text	IEC 60947-2
European directive WEEE	concerned

**Use conditions**

Operating temperature	-25...70 °C
Altitude	2000 m
Storage/transport temperature	-35...70 °C