



HNC041H

**Moulded Case Circuit Breaker h250 4P 50kA 40A LSI**

**Technical properties**

**Architecture**

Type of order	Toggle
Number of poles	4 P
Type of pole	4P4D N:0/50/100%

**Functions**

Complete device with protection unit	Yes
Trip Unit	LSI
Integrated earth fault protection	No

**Configuration**

Number of modules	8
-------------------	---

**Main electrical features**

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	40 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	7.5 kA
Thermal protection nob setting xIN	0.4 / 0.5 / 0.63 / 0.8 / 0.9 / 0.95 / 1
Thermal setting current on neutral pole	0 / 0.5 / 1 In
Breaking capacity on 1 pole for IT 230V NF 60947-2	60 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	50 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA

### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

### Power

Total power loss under IN	1.9 W
Power loss per pole at In	0.6 W

### Tripping

Tripmode	LSI
Thermal protection trip time	5 / 8 / 11 / 21 ms
Time of response when opening	10 ms

### Electrical specifications

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

### Installation, mounting

DIN rail mounting with optional adaptor	No
---	----

### Connection

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal

### Settings

Range of the magnetic adjustment	224 / 280 / 350 / 448 / 504 / 532 / 560 A
Magnetic protection nob setting xIN	2.5 / 5 / 10
Setting type In or Ith	IrTh

### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

### Use cases

Category of use	A
-----------------	---

**Standards**

---

Standard text	IEC 60947-2
European directive WEEE	concerned

---

**Safety**

---

Protection index IP	IP4X
---------------------	------

---

**Use conditions**

---

Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C

---