



HR502

EARTH LEAKAGE RELAY 0.3A INSTANT TRIP

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U_e	230 V
---------------------------------	-------

Voltage

Max operating voltage	276 V
-----------------------	-------

Electric current

Rated residual operating current	300 mA
Torroids : Allowed overload	30kA / 100ms

Power

Power consumed	3 VA
----------------	------

Connection

Connection cross-sect. flexible conductor	1 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 4mm ²
Connection cross-section in flexible cable for the measurement	1 / 2.5 mm ²
Connection cross-section in massive cable for the measurement	1.5 / 4 mm ²

Settings

Time delay of residual current	0 s
--------------------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
Residual current type	A
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...55 °C
Altitude	2000 m
Storage/transport temperature	-20...70 °C