



HXA024H

Alarm contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 250 V |
| Type of supply voltage | AC/DC |

Voltage

| | |
|---------------------------------|--------|
| Rated impulse withstand voltage | 1500 V |
| Rated operational voltage in DC | 125 V |

Electric current

| | |
|---------------|-----|
| Rated current | 3 A |
|---------------|-----|

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 3 W |
|---------------------------|-----|

Connection

| | |
|--------------------|---------------|
| Type of contacts | 1 NO/NC |
| Type of connection | quick connect |

Equipment

| | |
|---|---|
| Number of auxiliary contacts as normally closed contact | 1 |
| Number of auxiliary contacts as normally open contact | 1 |
| Number of auxiliary contacts as change-over contact | 0 |
| Number of auxiliary contacts as fault signal | 2 |

Standards

| | |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|