



HR500

Earth Leakage Relay 0.03A instantaneous Trip Type A

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U_e	230 V
---------------------------------	-------

Voltage

Max operating voltage	276 V
-----------------------	-------

Electric current

Rated residual operating current	30 mA
----------------------------------	-------

Torroïds : Allowed overload	30kA / 100ms
-----------------------------	--------------

Power

Power consumed	3 VA
----------------	------

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 2,5mm ²
---	------------------------

Connection cross-sect. rigid cable	1,5 / 4mm ²
------------------------------------	------------------------

Connection cross-section in flexible cable for the measurement	1 / 2.5 mm ²
--	-------------------------

Connection cross-section in massive cable for the measurement	1.5 / 4 mm ²
---	-------------------------

Settings

Time delay of residual current	0 s
--------------------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
---------------------	------

Residual current type	A
-----------------------	---

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Altitude	2000 m
----------	--------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------