



HXA051H

UVR delayed 24V DC (x160-P160-x250-P250-x630-P630)

Technical properties

Voltage

DC control voltage	24 V
Command voltage AC	0 V

Power

Total power loss under IN	0.6 W
---------------------------	-------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m