



**Insulated busbar 1P 63A prong 10mm<sup>2</sup> brown 13M**

**Technical properties**

**Architecture**

Number of poles	1 P
Type of pole	1 P

**Configuration**

Number of modules	13
-------------------	----

**Compatibility**

Intended for the compatible references	Modular devices
--	-----------------

**Main electrical features**

Rated operational voltage Ue	415 V
------------------------------	-------

**Voltage**

Max operating voltage	230 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Length	228 mm
Pitch	17.8 mm
Fixation distance in module steps	1

**Power supply**

Number of phases for the power supply	1 phase
---------------------------------------	---------

**Installation, mounting**

Suitable to a device with an auxiliary	No
--	----

**Connection**

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Suitable for product with neutral busbar	No
Connector type	busbar prong
Type of connection	with screw

**Equipment**

Number of appliances to build in	13
----------------------------------	----

**Safety**

REACH conform	Yes
---------------	-----

KB163P

RoHS conform

Yes

**Use conditions**

---

Insulated

Yes