



HZI811

**Controller**

**Technical properties**

**Architecture**

Fixing mode Din-Rail

**Configuration**

Number of modules 6

**Main electrical features**

Frequency 50/60 Hz

**Dimensions**

Depth of installed product 58 mm

Height of installed product 93 mm

Width of installed product 106 mm

**Power**

Power consumed 7.5 VA

**Measurement**

Frequency measuring range 50 to 60 Hz

Voltage measurement range 110 to 400 V

**Equipment**

Type of display LCD

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP2X

**Use conditions**

Operating temperature -20...60 °C

Altitude 2000 m

Storage/transport temperature -20...60 °C