



KB190B

Insulated busbar 1P 100A prong 20mm² 57M

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Configuration

Number of modules	57
-------------------	----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	100 A
---------------	-------

Dimensions

Length	1000 mm
Pitch	17.8 mm
Fixation distance in module steps	1

Power supply

Number of phases for the power supply	1 phase
---------------------------------------	---------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	20mm ²
Suitable for product with neutral busbar	No
Connector type	busbar prong
Type of connection	with screw

Equipment

Number of appliances to build in	57
----------------------------------	----

Safety

REACH conform	No
---------------	----

RoHS conform

Yes

Use conditions

Insulated

Yes