



KB190B

**Insulated busbar 1P 100A prong 20mm<sup>2</sup> 57M**

**Technical properties**

**Architecture**

Number of poles	1 P
Type of pole	1 P

**Configuration**

Number of modules	57
-------------------	----

**Compatibility**

Intended for the compatible references	Modular devices
--	-----------------

**Main electrical features**

Rated operational voltage Ue	415 V
------------------------------	-------

**Voltage**

Max operating voltage	230 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Length	1000 mm
Pitch	17.8 mm
Fixation distance in module steps	1

**Power supply**

Number of phases for the power supply	1 phase
---------------------------------------	---------

**Installation, mounting**

Suitable to a device with an auxiliary	No
--	----

**Connection**

Connection cross-sect. rigid cable	20mm <sup>2</sup>
Suitable for product with neutral busbar	No
Connector type	busbar prong

**Equipment**

Number of appliances to build in	57
----------------------------------	----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

---

REACH conform	No
RoHS conform	Yes

---

**Use conditions**

---

Insulated	Yes
-----------	-----

---