



HZI811

**Controller**

**Technical properties**

**Functions**

Precision class	Class 3
-----------------	---------

**Configuration**

Number of modules	6
-------------------	---

**Main electrical features**

Frequency	50/60 Hz
-----------	----------

**Dimensions**

Depth of installed product	58 mm
Height of installed product	93 mm
Width of installed product	106 mm

**Power**

Power consumed	7.5 VA
----------------	--------

**Measurement**

Frequency measuring range	50 to 60 Hz
Voltage measurement range	110 to 400 V

**Connection**

Connection cross-sect. flexible conductor	1,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5mm <sup>2</sup>
Type of connection	with screw

**Equipment**

Type of display	LCD
-----------------	-----

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-20...60 °C
Altitude	2000 m
Storage/transport temperature	-20...60 °C