



KB263A

Insulated busbar 2P 63A prong 10mm² 12M

Technical properties

Architecture

Number of poles	2 P
Type of pole	2 P

Configuration

Number of modules	12
-------------------	----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	210 mm
Pitch	17.8 mm
Fixation distance in module steps	2

Power supply

Number of phases for the power supply	2 phases
---------------------------------------	----------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	10mm ²
Suitable for product with neutral busbar	Yes
Connector type	busbar prong
Type of connection	with screw

Equipment

Number of appliances to build in	6
----------------------------------	---

Safety

REACH conform	No
---------------	----

RoHS conform

Yes

Use conditions

Insulated

Yes