



KB263C

## Insulated busbar 2P 63A prong 10mm<sup>2</sup> 24M

### Technical properties

#### Architecture

Number of poles 2 P

#### Configuration

Number of modules 24

#### Compatibility

Intended for the compatible references Modular devices

#### Main electrical features

Rated operational voltage Ue 230 / 400 V

#### Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

#### Electric current

Rated current 63 A

#### Dimensions

Length 420 mm

Pitch 17.8 mm

Fixation distance in module steps 2

#### Power supply

Number of phases for the power supply 2 phases

#### Installation, mounting

Suitable to a device with an auxiliary No

#### Connection

Connection cross-sect. rigid cable 10mm<sup>2</sup>

Suitable for product with neutral busbar Yes

Connector type busbar prong

#### Equipment

Number of appliances to build in 12

#### Standards

European directive WEEE concerned

#### Safety

REACH conform	No
RoHS conform	Yes
<b>Use conditions</b>	
Insulated	Yes