



KB263C

## Insulated busbar 2P 63A prong 10mm<sup>2</sup> 24M

### Technical properties

#### Architecture

Number of poles	2 P
Type of pole	2 P

#### Configuration

Number of modules	24
-------------------	----

#### Compatibility

Intended for the compatible references	Modular devices
--	-----------------

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

#### Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Length	420 mm
Pitch	17.8 mm
Fixation distance in module steps	2

#### Power supply

Number of phases for the power supply	2 phases
---------------------------------------	----------

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Suitable for product with neutral busbar	Yes
Connector type	busbar prong
Type of connection	with screw

#### Equipment

Number of appliances to build in	12
----------------------------------	----

#### Safety

REACH conform	No
---------------	----

RoHS conform

Yes

**Use conditions**

---

Insulated

Yes