



KB363B

Insulated busbar 3P 63A prong 10mm² 57M

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 3 P |
| Type of pole | 3 P |

Configuration

| | |
|-------------------|----|
| Number of modules | 57 |
|-------------------|----|

Compatibility

| | |
|--|-----------------|
| Intended for the compatible references | Modular devices |
|--|-----------------|

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 400 V |
|------------------------------|-------------|

Voltage

| | |
|---------------------------------|-------|
| Max operating voltage | 400 V |
| Rated impulse withstand voltage | 4 kV |

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Dimensions

| | |
|--------|---------|
| Length | 1000 mm |
| Pitch | 17.8 mm |

Power supply

| | |
|---------------------------------------|---------|
| Number of phases for the power supply | 3-phase |
|---------------------------------------|---------|

Installation, mounting

| | |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

Connection

| | |
|--|-------------------|
| Connection cross-sect. rigid cable | 10mm ² |
| Suitable for product with neutral busbar | No |
| Connector type | busbar prong |
| Type of connection | with screw |

Equipment

| | |
|----------------------------------|----|
| Number of appliances to build in | 19 |
|----------------------------------|----|

Safety

| | |
|---------------|-----|
| REACH conform | No |
| RoHS conform | Yes |

