



KB463A

Insulated busbar 3P+N 63A prong 10mm² 12M

Technical properties

Architecture

Number of poles 4 P

Configuration

Number of modules 12

Compatibility

Intended for the compatible references Modular devices

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

Electric current

Rated current 63 A

Dimensions

Length 210 mm

Pitch 17.8 mm

Fixation distance in module steps 4

Power supply

Number of phases for the power supply 3 phases

Installation, mounting

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 10mm²

Suitable for product with neutral busbar Yes

Connector type busbar prong

Equipment

Number of appliances to build in 3

Standards

European directive WEEE concerned

Safety

| | |
|-----------------------|-----|
| REACH conform | No |
| RoHS conform | Yes |
| Use conditions | |
| Insulated | Yes |