



KB480B

Insulated busbar 3P+N 80A prong 16mm² 57M

Technical properties

Architecture

Number of poles 4 P

Configuration

Number of modules 57

Compatibility

Intended for the compatible references Modular devices

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

Electric current

Rated current 80 A

Dimensions

Length 1000 mm

Pitch 17.8 mm

Fixation distance in module steps 4

Power supply

Number of phases for the power supply 3 phases

Installation, mounting

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 16mm²

Suitable for product with neutral busbar Yes

Connector type busbar prong

Equipment

Number of appliances to build in 14

Standards

European directive WEEE concerned

Safety

REACH conform	No
RoHS conform	Yes
Use conditions	
Insulated	Yes