



KB463C

Insulated busbar 3P+N 63A prong 10mm² 24M

Technical properties

Architecture

Number of poles	4 P
Type of pole	3P+N

Configuration

Number of modules	24
-------------------	----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	420 mm
Pitch	17.8 mm
Fixation distance in module steps	4

Power supply

Number of phases for the power supply	3-phase
---------------------------------------	---------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	10mm ²
Suitable for product with neutral busbar	Yes
Connector type	busbar prong
Type of connection	with screw

Equipment

Number of appliances to build in	6
----------------------------------	---

Standards

European directive WEEE

concerned

Use conditions

Insulated

Yes