



KB463C

## Insulated busbar 3P+N 63A prong 10mm<sup>2</sup> 24M

### Technical properties

#### Architecture

Number of poles	4 P
-----------------	-----

#### Configuration

Number of modules	24
-------------------	----

#### Compatibility

Intended for the compatible references	Modular devices
--	-----------------

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

#### Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Length	420 mm
Pitch	17.8 mm
Fixation distance in module steps	4

#### Power supply

Number of phases for the power supply	3-phase
---------------------------------------	---------

#### Materials

Colour	stone grey
--------	------------

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Suitable for product with neutral busbar	Yes
Type of connection	with screw

#### Equipment

Number of appliances to build in	6
----------------------------------	---

#### Standards

European directive WEEE	concerned
-------------------------	-----------

<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
<b>Use conditions</b>	
Insulated	Yes