



**Insulated busbar 3P+N 63A prong 10mm<sup>2</sup> 48C for MCB 1P+N 1 module**

**Technical properties**

**Architecture**

Number of poles	4 P
Type of pole	3P+N

**Configuration**

Number of modules	24
-------------------	----

**Compatibility**

Intended for the compatible references	MCB 1P+N
--	----------

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

**Voltage**

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Length	428 mm
Pitch	17.8 mm

**Power supply**

Number of phases for the power supply	3 phases
---------------------------------------	----------

**Installation, mounting**

Suitable to a device with an auxiliary	No
--	----

**Connection**

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Suitable for product with neutral busbar	Yes
Connector type	busbar prong
Type of connection	with screw

**Equipment**

Number of appliances to build in	6
----------------------------------	---

**Use conditions**

Insulated	Yes
-----------	-----

KBN663C